



The Habitat Portable Shower System

Similar to all Habitat portable shelters the shower system features an articulated aluminum mainframe, snap lock eave and base bars and Velcro fastened cover system. Standard shower shelters provide zippered entries, while optional integrated aluminum framed doors are available. The fabric cover is the same tough, 14 oz. vinyl coated polyester used on all of our shelters. Standard opaque vinyl skylight panels in the roof lend an open atmosphere to the inside of the shower. Shower catch basins are plumbed for the recovery of gray water.

Standard double shower configuration is two individual shower stalls with zippered entry doors. The assembled shower measures 90" x 46" and comes packaged in one durable vinyl field bag. The shower can also be configured as a single stall with dressing room.

Water distribution manifolds are provided with two individually controlled low volume nozzles. No tools are required for assembly. Optional flexible, elevated shower floor matting is available and rolls up to store in the shower transport bag.

The portable shower self-priming sump pump is designed to evacuate water from the shower basin and discharge to an appropriate collection point or device such as a gray water bladder. Equipped with a specially designed suction hose and strainer, the sump will keep water levels in the basin below 1/8". The pump has run dry capabilities and will not be damaged if the water source is shut down. **NOT FOR USE WITH FLAMMABLE LIQUIDS.**



DESIGN SHELTER INC.





The Habitat Portable Ablution System

Similar to all Habitat portable shelters the ablation system features an articulated aluminum mainframe, snap lock eave and base bars and Velcro fastened cover system. Standard ablation shelters provide zippered door entries, while optional integrated aluminum framed doors are available. The exterior cover is the same tough, 14 oz. vinyl coated polyester used on all of our shelters. Standard opaque vinyl skylight panels in the roof lend an open atmosphere to the inside of the ablation shelter proper.



The Design Shelter ablation station is a single stall, field toilet shelter. It is quickly and easily assembled in the field without tools and provides full privacy for the user. The interior floor and cabinet is a one-piece formed aluminum plate assembly that folds flat for storage or transport. A collapsible Coroplast containment box is lined with disposable poly-bags for disposition of wastes and is compatible with commercially available human waste gelling agents.

If your team requires a simple and easy to erect single use ablation station for your field operations, the Habitat portable ablation system from Design Shelter Inc. delivers.

“Not Your Ordinary Tent”

DESIGN SHELTER INC.

MAILING ADDRESS: DESIGN SHELTER INC., P.O. BOX 1445, STN. "B", MISSISSAUGA, ONTARIO, CANADA L4Y 4G2
PHONE (604) 921-8805 • FAX (604) 921-8806 • WEBSITE www.designshelter.com • EMAIL info@designshelter.com

DSIDC.02.03

